









Keuze- en bestelgegevens

Bouwgrootte	Bouwbreedte	I_n	U_n	Spanningvoerende trekoren	Gewicht 1 stuk ca.	PKG*/VPE	
	mm	A	V	Bestelnr.	kg	Stuks	
Mespatronen met bovenmelder, bedrijfsklasse aM							
	000	21	6	AC 500 V	3ND1 801	0,130	3
			10		3ND1 803	0,130	3
			16		3ND1 805	0,130	3
			20		3ND1 807	0,130	3
			25		3ND1 810	0,130	3
			32		3ND1 812	0,130	3
			35		3ND1 814	0,130	3
			40		3ND1 817	0,130	3
			50		3ND1 820	0,130	3
			63		3ND1 822	0,130	3
			80		3ND1 824	0,130	3
	00	30	100	AC 500 V	3ND1 830	0,192	3
			125		3ND1 832	0,192	3
			160		3ND1 836	0,192	3
	1	30	63	AC 690 V	3ND2 122	0,290	3
			80		3ND2 124	0,290	3
			100		3ND2 130	0,440	3
		47,2	125		3ND2 132	0,440	3
			160		3ND2 136	0,440	3
			200		3ND2 140	0,440	3
			250		3ND2 144	0,440	3
	2	47,2	125	AC 690 V	3ND2 232	0,440	3
			160		3ND2 236	0,440	3
			200		3ND2 240	0,440	3
		57,8	250		3ND2 244	0,440	3
			315		3ND2 252	0,650	3
			355		3ND2 254	0,650	3
400	3ND2 260	0,650	3				
	3	57,8	315	AC 690 V	3ND2 352	0,650	3
			355		3ND2 354	0,650	3
			400		3ND2 360	0,650	3
		71,2	500		3ND1 365	1,030	3
			630		3ND1 372	1,000	3

Smeltveiligheden Zekeringen

Cilindrische zekeringen aM

Keuze- en bestelgegevens

	Bouwgrootte	I_n	U_n	Bedrijfsklasse aM	Gewicht 1 stuk ca.	PKG*/ VPE
	mm × mm	A	AC V	Bestelnr.	kg	Stuks
Cilindrische zekeringen						
	10 × 38	0,5	500	3NW8 000-1	0,003	10
		1		3NW8 011-1	0,008	10
		2		3NW8 002-1	0,008	10
		4		3NW8 004-1	0,008	10
		6		3NW8 001-1	0,008	10
		8		3NW8 008-1	0,003	10
		10		3NW8 003-1	0,008	10
		12		3NW8 006-1	0,008	10
		16		3NW8 005-1	0,008	10
		20		3NW8 007-1	0,008	10
		25	400	3NW8 010-1	0,008	10
	14 × 51	2	500	3NW8 102-1	0,019	10
		4		3NW8 104-1	0,019	10
		6		3NW8 101-1	0,019	10
		8		3NW8 108-1	0,019	10
		10		3NW8 103-1	0,019	10
		12		3NW8 106-1	0,019	10
		16		3NW8 105-1	0,019	10
		20		3NW8 107-1	0,019	10
		25		3NW8 110-1	0,019	10
		32		3NW8 112-1	0,019	10
		40	400	3NW8 117-1	0,019	10
		50	400	3NW8 120-1	0,019	10
	22 × 58	10	500	3NW8 203-1		
		12		3NW8 206-1	0,051	10
		16		3NW8 205-1	0,051	10
		20		3NW8 207-1	0,051	10
		25		3NW8 210-1	0,051	10
		32		3NW8 212-1	0,051	10
		40		3NW8 217-1	0,051	10
		50		3NW8 220-1	0,051	10
		63		3NW8 222-1	0,051	10
		80		3NW8 224-1	0,051	10
		100	400	3NW8 230-1	0,051	10