



1/3" High resolution monochrome cameras


CCBB1325-LC
CCBB1325-MC

- Easy on-screen adjustment of all operating parameters
- Six back-light compensation zones
- Available in 12 V DC / 24 V AC and 230 V AC versions
- Compatible with infrared illuminators
- Camera title on video
- Cable management bracket for lens cable
- Supports both direct drive and video drive auto-iris lenses

CCBB1325 uses the latest CCD technology and advanced digital signal processing techniques to provide crisp, aperture corrected images for surveillance applications requiring high resolution images. Great low-light sensitivity, electronic shutter, automatic gain control and back-light compensation enable this camera to operate in a wide range of lighting conditions.

- **Easy setup**
All camera adjustments are performed via an intuitive on-screen menu that is navigated via five touch-keys on the side panel.
- **Excellent IR sensitivity**
CCBB1325 is the ideal choice for night-time surveillance when used in conjunction with both solid-state (LED) and halogen type infrared illuminators.
- **Electronic Shutter**
The electronic shutter automatically adjusts from 1/50 to 1/100,000 of a second in response to varying light levels, enabling the use of manual and auto iris lenses in a wide variety of situations.

Dimensions and controls



Rear View 90~260 V AC
CCBB1325-MC

Rear View 12 V DC / 24 V AC
CCBB1325-LC

Side View of controls

Technical data

Television standard	625 lines, 50 fields/s, 50 Hz (vertically), 15.625 Hz (horizontally)
Image sensor	1/3 inch interline CCD 752 x 582 active pixels
Horizontal resolution	580 lines
Minimum illumination	0.15 Lux (F1.2, AGC On) at 50 IRE
Camera title	16 character title (positioned anywhere on screen)
Electronic shutter	Manual shutter: 1/50, 1/100, 1/250, 1/400, 1/1000, 1/2000, 1/5000, 1/10000 sec Automatic shutter: AES 1/50 to 1/100,000 sec
Back-light compensation	6 zones: Centre 1, Centre 2, Doorway 1, Doorway 2 , Top Half, Bot Half
Video output	1Vpp composite (75 Ohm), BNC
Automatic gain control (AGC)	5 maximum levels can be selected: OFF / 12 dB / 18 dB / 24 dB / 30 dB / 38 dB (Sens up)
Signal/noise ratio	> 50 dB
Gamma	Selectable: 0.45, 0.8, 1 (typical: 0.45)
Lens control	Direct drive or Video drive
Synchronisation	Internal: with crystal External: mains synchronisation
Recommended power source	CCBB1325-LC: 12 V DC or 24 V AC, 10 VA CCBB1325-MC: 100~240 V AC \pm 10%
Power consumption	3.8 W
Temperature range (operating)	-10 to +50°C
Relative humidity	30 to 95 %, non-condensing
Dimensions (W x H x D)	70 x 58 x 117 mm
Weight	CCBB1325-LC: 0.6 kg CCBB1325-MC: 0.7 kg

Details for ordering

Type	Part no.	Designation	Weight
CCBB1325-LC	2GF1083-8BA	1/3" DSP High Resolution CCIR Camera 580TVL 12 V DC or 24 V AC, 50 Hz	0.6 kg
CCBB1325-MC	2GF1083-8DA	1/3" DSP High Resolution CCIR Camera 580TVL 90~260 V AC, 50 Hz	0.7 kg