




### Sélection et références de commande

| Version   | $U_e$                           | $I_e$ | $U_c$ | UM         | N° de référence | Poids<br>1 pièce<br>kg | UDC*/<br>UE<br>Pièce |   |
|---|---------------------------------|-------|-------|------------|-----------------|------------------------|----------------------|---|
|   | AC V                            | AC A  | AC V  |            |                 |                        |                      |   |
| <br>5TT4 201-0 | <b>Relais de commutation</b>    |       |       |            |                 |                        |                      |   |
|   | 1 contact NO                    | 250   | 16    | 230        | 1               | 5TT4 201-0             | 0,126                | 1 |
|   |                                 |       |       | 115        |                 | 5TT4 201-1             | 0,120                | 1 |
|   |                                 |       |       | 24         |                 | 5TT4 201-2             | 0,120                | 1 |
|   |                                 |       |       | 12         |                 | 5TT4 201-3             | 0,118                | 1 |
|   | 2 contacts NO                   | 400   | 16    | 8          | 1               | 5TT4 201-4             | 0,124                | 1 |
|   |                                 |       |       | 230        |                 | 5TT4 202-0             | 0,137                | 1 |
|   |                                 |       |       | 115        |                 | 5TT4 202-1             | 0,131                | 1 |
|   |                                 |       |       | 24         |                 | 5TT4 202-2             | 0,131                | 1 |
|   | 4 contacts NO                   | 400   | 16    | 12         | 2               | 5TT4 202-3             | 0,129                | 1 |
|   |                                 |       |       | 8          |                 | 5TT4 202-4             | 0,135                | 1 |
|   |                                 |       |       | 230        |                 | 5TT4 204-0             | 0,270                | 1 |
|   |                                 |       |       | 115        |                 | 5TT4 204-1             | 0,258                | 1 |
|   | 1 contact NO,<br>+ 1 contact NF | 400   | 16    | 24         | 1               | 5TT4 204-2             | 0,259                | 1 |
|   |                                 |       |       | 12         |                 | 5TT4 204-3             | 0,254                | 1 |
|   |                                 |       |       | 8          |                 | 5TT4 204-4             | 0,266                | 1 |
|   |                                 |       |       | 230        |                 | 5TT4 205-0             | 0,137                | 1 |
|   | 1 contact inverseur             | 250   | 16    | 115        | 1               | 5TT4 205-1             | 0,131                | 1 |
|   |                                 |       |       | 24         |                 | 5TT4 205-2             | 0,131                | 1 |
|   |                                 |       |       | 12         |                 | 5TT4 205-3             | 0,129                | 1 |
|   |                                 |       |       | 8          |                 | 5TT4 205-4             | 0,135                | 1 |
|   | 2 contacts inverseurs           | 400   | 16    | 230        | 1               | 5TT4 206-0             | 0,127                | 1 |
|   |                                 |       |       | 115        |                 | 5TT4 206-1             | 0,121                | 1 |
|   |                                 |       |       | 24         |                 | 5TT4 206-2             | 0,122                | 1 |
|   |                                 |       |       | 12         |                 | 5TT4 206-3             | 0,120                | 1 |
|   |                                 |       |       | 8          |                 | 5TT4 206-4             | 0,125                | 1 |
|   |                                 |       |       | 230        |                 | 5TT4 207-0             | 0,140                | 1 |
|   |                                 |       |       | 115        |                 | 5TT4 207-1             | 0,134                | 1 |
| 24  |                                 |       |       | 5TT4 207-2 |                 | 0,135                  | 1                    |   |
|   |                                 |       | 12    |            | 5TT4 207-3      | 0,133                  | 1                    |   |
|   |                                 |       | 8     |            | 5TT4 207-4      | 0,138                  | 1                    |   |