



# Hybrid Video Recorder SISTORE MX 3G DVD

with built-in DVD burner  
V2.8x



SISTORE MX1608 1000/300 DVD  
SISTORE MX1608 2000/300 DVD  
SISTORE MX1608 3000/300 DVD  
SISTORE MX1616 1000/500 DVD  
SISTORE MX1616 2000/500 DVD  
SISTORE MX1616 3000/500 DVD

SISTORE MX is a hybrid recording and video monitoring system. It provides reliable local recording for both analogue and IP cameras with flexible remote monitoring via LAN or ISDN.

- Hybrid monitoring and digital video recording system for up to 16 analogue and 16 IP cameras
- Certified according to BGV-Kassen and Fiducia (Banking approval)
- Kalagate certified watermarking for enhanced image tamper protection
- Recording speed of up to 400 images per second (analogue) and up to 400 images per second (digital)
- Camera sabotage detection (camera repositioning/spraying)
- Search Mask capability (Motion search/Smart Search) for search within recorded video locally and from the RemoteView station
- Pentaplex operation (simultaneous display, recording and playback of live images)
- Temperature management for enhanced system reliability
- High image quality with up to full 4CIF recording for analogue cameras and up to 5 Megapixel for IP cameras (dependent on camera model)
- Supports most leading IP cameras including Siemens, Axis, JVC and others
- Graphical user interface for intuitive operation, reduced training needs and enhanced productivity
- Simultaneous display of up to 32 live images (multiplexed), also in RemoteView
- Direct connection to RemoteView upon alarm, including alarm processing
- Automatic messaging (e.g. alarms, failure) via e-mail or SMS
- Built-in DVD burner for easy archiving

- Powerful search capabilities using timeline, logbook, Smartsearch, ATM data or date/time assist in the rapid location of required video footage
- Simple intuitive operation and configuration reduces commissioning time
- Simultaneous search of up to 4 cameras locally and remotely over LAN or ISDN
- Connection of up to 4 analogue video monitors and basic video matrix function 16/4 (static, alarm, motion, PTZ, sequencing)
- Configurable pre-alarm recording per camera enhances functional flexibility
- Intelligent motion detection individually configurable for each camera
- PTZ control for dome and pan-and-tilt units possible from the RemoteView station via a CKA48xx control unit
- Multi-client function for access of up to 16 clients to one SISTORE MX
- Virtual guard tour on the RemoteView station for automatic connection of several sites assists in managing distributed or multisite systems
- Status indication of the switch outputs also via RemoteView
- Reference Image function facilitates camera maintenance by allowing an easy comparison of actual camera position and image quality with "as installed" settings
- Bandwidth limiting for remote viewing over low-bandwidth connections
- Watchdog function to ensure safe and reliable operation
- Control via Video Software IVM
- Interface to SiPass access control system provides interoperability
- Interface connection to CDM (ATM) or POS via SISTORE MX interface box
- Embedded hardware utilising the latest Texas Instruments "DaVinci" DSPs

## Functionalities

### ■ Display mode

The display mode is the unit's normal operating mode. In addition to live images displayed from selected cameras, all events such as loss of video, alarms and malfunctions are logged and reported in an easy to use overview screen.

### ■ Playback mode

The playback mode is used to review recorded video footage. SISTORE MX allows flexible and precise searching for specific events to quickly find the required video footage. Access to playback/searching is regulated via administrative permission levels and can be restricted using 4-eyes principle. The MX has pentaplex capability so playing back footage does not affect either live view or recording speed. Archiving of video footage is possible to standard USB 2.0 devices or to the built-in DVD burner.

### ■ Configuration mode

Configuration mode is used for the following operations:

- Administration of user rights
- Configuration of the analogue and digital (IP) cameras including brightness, contrast and colour saturation, as well as digital inputs and outputs and serial inputs
- Camera parameter settings for motion detection, alarm contacts, signal outputs
- Time control, alarm forwarding, transmission, e-mail and SMS
- Network parameters, such as ISDN or LAN with bandwidth limitation

### ■ Details for ordering

Type	Part no	Designation	Weight*
SISTORE MX1608 1000/300 DVD	S54569-C201-B3	SISTORE MX 1608 3G HVR, DVD, 1 TB, 300 ips	approx. 11.6 kg
SISTORE MX1608 2000/300 DVD	S54569-C201-B5	SISTORE MX 1608 3G HVR, DVD, 2 TB, 300 ips	approx. 12.3 kg
SISTORE MX1608 3000/300 DVD	S54569-C201-B7	SISTORE MX 1608 3G HVR, DVD, 3 TB, 300 ips	approx. 12.9 kg
SISTORE MX1616 1000/500 DVD	S54569-C202-B3	SISTORE MX 1616 3G HVR, DVD, 1 TB, 500 ips	approx. 11.6 kg
SISTORE MX1616 2000/500 DVD	S54569-C202-B5	SISTORE MX 1616 3G HVR, DVD, 2 TB, 500 ips	approx. 12.3 kg
SISTORE MX1616 3000/500 DVD	S54569-C202-B7	SISTORE MX 1616 3G HVR, DVD, 3 TB, 500 ips	approx. 12.9 kg

\* Device incl. packing material, accessories that are included in the delivery, and documentation

Further products and accessories can be found in the Internet: [siemens.com/cctv](http://siemens.com/cctv) > **Catalogue Downloads.**

### Accessories (included in the delivery)

- Installation Manual
- Mouse
- EU power cord

## ■ Technical data

Recording speed	16 channel models: 400 ips (analogue) @ 4CIF / 100 ips (digital) 8 channel models: 200 ips (analogue) @ 4CIF / 100 ips (digital) individually configurable for each camera
Video inputs	8/16 analogue (CVBS, BNC) 1 V <sub>SS</sub> (75 Ohm) looped to 8/16 outputs 16 IP camera inputs via network on MX1608/MX1616
Video outputs	4 (CVBS, BNC), 1 V <sub>SS</sub> (75 Ohm)
Audio inputs	8/16 (line in, spring clamp) Note: Audio feature planned for later firmware
Audio outputs	4 (line out, spring clamp) Note: Audio feature planned for later firmware
Network connections	2 x 10/100/1000 Base-T (RJ-45)
Digital inputs/outputs (opto-isolated, spring clamp)	16 alarm inputs, 4 digital inputs 4 digital outputs (5 – 24 V, max. 50 mA)
Event control	Event-triggered recording of individual cameras or camera groups with configurable time-slot pattern Events: alarm contacts, motion detection, time control, TCP/IP command
Alarm signalling	Via monitor connection, digital output, LAN/WAN to RemoteView station
Interfaces	2 x RS485 / 6 USB 2.0 / 1 DVI-I (including VGA) / 1 DVI-D
Video standard	PAL
Resolution	Analogue: CIF/2CIF/4CIF IP-cameras: max. 5 megapixels depending on the camera
Compression	Recording: MJPEG, configurable data rate Transmission to RemoteView: MJPEG/MPEG4 (max. 2048 x 1536)
Hard disk capacity	Max. 3 hard disks SATA (1 TB each)
Backup recording media	Network / USB / built-in DVD burner
Display resolution	Max. 2048 x 1536 (4:3 and 16:10 layouts supported)
Playback	Individual images, video sequence (replay rate configurable between 0.1 to 50 times), forward/backward, pause (frozen image)
Image search	By means of date, time, camera number, recording event, logbook, SmartSearch
Power supply	110 – 240 V (± 10 %), 50/60 Hz, max. 150 W
Ambient temperature, operating	5 – 40 °C
Relative humidity	20 – 80 %, no condensation
Design variants	Desktop, 19" rack mountable, 2 RU
Dimensions (W x H x D)	430 x 87 x 440 mm

The information in this document contains general descriptions of technical options available, which do not always have to be present in individual cases. The required features should therefore be specified in each individual case at the time of closing the contract.

© Siemens Building Technologies • Document no. A6V10260888 • Edition: 28.10.2009 • Document version: 1.2

[www.buildingtechnologies.siemens.com](http://www.buildingtechnologies.siemens.com)

Siemens Building Technologies  
Fire & Security Products GmbH & Co. oHG  
Industry Sector  
Siemensallee 84  
D-76187 Karlsruhe  
Tel. +49 721 595 1